

O₂ Conserver

OXYMO

- Adjustable flow from 0 to 7,5 L/min. Minimum delay in the bolus.
- Adjustable trigger between -0,5 and -9,5 cmH₂O.
- Electrical supply: rechargeable battery, 2 x AA batteries or AC/CD adaptor.
- Pressure supply: 1 bar, from a standard regulator or liquid O₂.
- Alarm system: apnea, battery failure and interrupted O₂ supply.
- Visual display: ventilation frequency (BPM).
- Alarm and event register: graphical PC software, downloadable and configurable through USB port.
- Safety password (optional).



OXYMO